

Garant

HT chuck, BT 40 short, Clamping range \varnothing D1: 20mm



Order data

Order number	303450 20
GTIN	4045197513090
Item class	31H

Description

Version:

- Very high overall stiffness due to optimised design.
- Axial length adjustment, adjustment travel 10 mm.

Advantage:

- Maximum transmissible torque 550 Nm, version HT (High Torque), for high process reliability.
- Ideal damping characteristics, resulting in optimum surface finishes, increased tool life and spindle protection.
- Temperature resistance up to 120 °C.

Application:

Especially for heavy-duty milling.

Supplied with:

Hexagon cross-bar wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308802.

Note:

Caution in the case of extra-long tools and TPC machining.

Technical description

Reach L_1	45 mm
Clamping \varnothing D ₁	20 mm
Overhang dimension A	72.5 mm

suitable reducing adapter	302160; 302155; 302150; 302165
External Ø D	49 mm
Adapter	BT 40 short
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Hydraulic clamping chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 40	308765 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40