

Garant
Side lock arbor, HSK-F 63 short, Clamping range \varnothing D1: 10mm

Order data

Order number	304306 10
GTIN	4045197584854
Item class	31A

Description
Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth cutting action!).

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890.

Note:

Without a thread for the coolant pipe.

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Clamping \varnothing D ₁	10 mm
Spare clamping screw No. 30 9900	10
Overhang dimension A	65 mm
External \varnothing D	35 mm
Adapter	HSK-F 63 short
Arbor standard	DIN 69893

Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1
Shape	F
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping Ø D1 10 mm	309900 10
--	-----------