

Garant
Face mill arbor vibration damped, BT 50 A = 300, Spigot \varnothing d1: 22mm

Order data

Order number	303055 22
GTIN	4045197821713
Item class	31A

Description
Version:

- **Cylindrical form.**
- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **With RFID/Balluffchip bore.**
- **Larger collar contact face.**
- **Vibration damped version, arbor with vibration-damping core.**

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special toggle spanner No. 309840.

Note:

Further sizes on request.

Technical description

Milling mandrel length L_4	19 mm
External \varnothing D	48 mm
Spigot \varnothing d ₁	22 mm
Overhang dimension A	300 mm
Adapter	BT 50 A = 300
Standard	DIN 6357
Arbor standard	DIN 69882-3

Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Accessories

Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Toggle spanner for mandrel Ø 22 mm	309840 22
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50