

Garant

Face mill arbor vibration-damped, conical, HSK-A 100 A = 200, Spigot \varnothing d1: 22 mm


Order data

Order number	306710 22
GTIN	4045197821836
Item class	31A

Description
Version:

- **Shank, spigot, and all contact surfaces are ground at the collar.**
- **With Balluffchip bore.**
- **Increased collar contact surface.**

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special coolant pipe wrench No. 309840, coolant pipe No. 309880.

Note:

Further sizes on request.

External \varnothing D: 80 mm

\varnothing D₂: 48 mm

Milling mandrel length L₄: 19 mm

Technical description

External \varnothing D	80 mm
Spigot \varnothing d ₁	22 mm
\varnothing D ₂	48 mm

Milling mandrel length L ₄	19 mm
Adapter	HSK-A 100 A = 200
Standard	DIN 6357
Arbor standard	DIN 69882-3
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 22 mm	309840 22
------------------------------------	-----------