

Garant
WCHX 10T308, Type: SM


Order data

Order number	268494 SM
GTIN	4045197470966
Item class	21K

Description

Suitable for:

Boring tool No. 268463 – 268468, size 20.

Technical description

Corner radius	0.2 mm
Main application	P
Type	SM
Cutting speed v_c secondary application	110 - 140 m/min
Secondary application	M
Cutting speed v_c main application	110 - 220 m/min
Grade	HB7120
Tool material	Carbide
ISO code indexable insert	WCHX 10T308
Number of changes/inserts	3

suitable for tool dia. D_c	20 mm
Type of product	Indexable insert for turning