



Angle grinder, Type: AGS15-125



Order data

Order number	077141 AGS15-125
GTIN	4002395236015
Item class	03M

Description

Version:

Milwaukee angle grinder with smooth start-up, **restart inhibit** and overload protection. 1500 W special angle grinder with throttled speed **for use with flap discs** with constant speed electronics. Including clamping set.

Supplied with:

Additional handle, guard cover, 4 m power cable.

Technical description

maximum disc Ø	125 mm
Manufacturer's designation	AGS15-125CProTector
Restart block	yes
maximum cutting depth	33 mm
Weight	2.4 kg
maximum vibration to EN	5.5 m/s ²
Power consumption	1500 W
Soft start	yes
Power supply	Mains operated
maximum speed	7600 min ⁻¹
Type of product	Angle grinder

Accessories

Clamping nut M14 Type NUT

073930 NUT

Clamping nut M14 Type FIXTEC

073930 FIXTEC