

**Garant****ER collet chuck, HSK-E 40 short, for ER collet size: 11****Order data**

Order number	305150 11
GTIN	4045197505033
Item class	31A

**Description****Version:**

- All shanks hard turned (for smooth running!).
- Through bored (without adjustment screw).
- HSK mating faces machined.

**Application:**

For clamping tools with plain shanks in ER collets to DIN 6499 – Form A and B.

**Supplied with:**

Coated high-speed clamping nut.

**Optional extras:**

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, ER collets No. 308881 – 309434, ER chuck key No. 309680 or 613300.

**Note:**

Without RFID/Balluffchip bore.

**Technical description**

Overhang dimension A	60 mm
for ER collets	11
Clamping range	0.5 - 7 mm
External Ø D	19 mm
Adapter	HSK-E 40 short

Arbor standard	DIN 69882-6
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	E
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

## Accessories

ER collet Nominal clamping Ø d 2,5 mm	308881 2,5
ER collet Nominal clamping Ø d 3 mm	308918 3
ER collet Nominal clamping Ø d 4 mm	308918 4
ER collet Nominal clamping Ø d 2 mm	308918 2
ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
ER collet Nominal clamping Ø d 4 mm	308881 4
ER collet Nominal clamping Ø d 1 mm	308881 1
ER collet Nominal clamping Ø d 5,5 mm	308881 5,5
Single open ended spanner Width across flats 17 mm	613300 17
ER collet Nominal clamping Ø d 3,5 mm	308881 3,5
ER collet set 13 pieces 1–7 mm	309010
ER collet Nominal clamping Ø d 1 mm	308918 1
ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER collet Nominal clamping Ø d 4,5 mm	308881 4,5
ER collet Nominal clamping Ø d 2 mm	308881 2
ER collet Nominal clamping Ø d 7 mm	308881 7
ER collet Nominal clamping Ø d 6 mm	308881 6
ER collet Nominal clamping Ø d 6 mm	308918 6

ER collet Nominal clamping Ø d 7 mm	308918 7
ER collet Nominal clamping Ø d 5 mm	308881 5
ER collet set 7 pieces 1–7 mm	309155
ER collet Nominal clamping Ø d 3 mm	308881 3
ER collet Nominal clamping Ø d 5 mm	308918 5