

Garant**WCHX 10T304, Type: SM****Order data**

Order number	268492 SM
GTIN	4045197470904
Item class	21K

Description**Suitable for:**

Boring tool No. 268463 – 268468, size 20.

Technical description

Cutting speed v_c secondary application	110 - 140 m/min
Secondary application	M
Cutting speed v_c main application	110 - 220 m/min
Main application	P
Corner radius	0.2 mm
Type	SM
Grade	HB7120
Tool material	Carbide
ISO code indexable insert	WCHX 10T304
Number of changes/inserts	3

suitable for tool dia. D_c	20 mm
Type of product	Indexable insert for turning