

**WB quick-change holder internal machining, Type / Internal Ø R: 4/60mm****Order data**

Order number	316200 4/60
GTIN	4045197318824
Item class	33P

Description**Application:**

To accept **Morse taper sleeves**, slotted sleeves and for **direct fitting of large boring bars** (type WB).

Technical description

Internal Ø R	60 mm
Type of product	Steel toolholder

Accessories

Clamping sleeve for plain shank Type / Clamping Ø 4/25 mm	316260 4/25
Clamping sleeve For MT shank Type 4/5	316240 4/5

Clamping sleeve for plain shank Type / Clamping Ø 4/32 mm	316260 4/32
Clamping sleeve For MT shank Type 4/4	316240 4/4
Clamping sleeve for plain shank Type / Clamping Ø 4/40 mm	316260 4/40
Clamping sleeve for plain shank Type / Clamping Ø 4/50 mm	316260 4/50