

Garant

Hydraulic chuck HT with cooling channel bores, HSK-A 63 short, Clamping range \varnothing D1: 16mm



Order data

Order number	307553 16
GTIN	4045197644831
Item class	31H

Description

Version:

- Very high total rigidity due to optimised design.
- With RFID/Balluffchip bore.
- Axial length adjustment, adjustment travel 10 mm.
- Flexible due to use of reducing sleeves.

Advantage:

- Very high transmitted torque (550 Nm), providing high process reliability.
- Ideal damping characteristics, resulting in optimum surface finishes, increased tool life and spindle protection.

Application:

- Especially for heavy-duty milling.
- For clamping tools with shank tolerance h6.

Supplied with:

Hexagon cross-bar wrench.

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, reducing adapters No. 302135 – 302187.

Note:

Caution in the case of extra-long tools and TPC machining.

Technical description

Clamping \varnothing D ₁	16 mm
---------------------------------------	-------

Reach L ₁	54 mm
Overhang dimension A	80 mm
External Ø D	52.5 mm
Adjustment travel V	10 mm
Adapter	HSK-A 63 short
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Hydraulic clamping chuck