

**Short taper chuck flange DIN 55027, Ø d1 / taper: 200/5mm****Order data**

Order number	317500 200/5
GTIN	4019208078670
Item class	33R

Description**Version:**

Finish machined on all sides.

Application:

For retrofitting to lathe chucks with recessed mount to DIN 6350 A. **Lathe chucks with incorporated short tapers are preferable due to shorter overhang.**

For spindle noses **DIN 55027** and ISO 702/III (equals the old standard **DIN 55022**) with studs and collar nuts.

Material:

C45 steel

Technical description

Thickness B	21 mm
Taper Ø d ₂	82.575 mm
Taper size	5
External Ø d ₁	200 mm

Number of studs	4
Type of product	Lathe chuck accessories