



## Self-centring lathe chuck with one-piece reversible jaws, DIN 702-3, Type: 250/8



### Order data

Order number	313130 250/8
GTIN	4019208227856
Item class	33R

### Description

#### Version:

- **Maximum concentricity and changeover accuracy.**
- **With jaw retention, centrally clamping.**
- **Large pass-through diameter.**
- **Accuracy twice that specified by DIN 6386.**
- **High clamping force with low force exertion.**
- **Higher speeds thanks to safety blocking slide.**
- **Jaws can quickly and easily be reversed or exchanged.**
- **Outer contour with drop-off wedge for water.**
- **Grease nipple for greasing all sliding faces.**

#### Advantage:

Wherever extremely high clamping forces, high concentricity, and reliable continuous repeatability are required.

#### Application:

For spindle noses DIN 702-3. With studs and collar nuts. The chuck is always fitted to the spindle nose directly without an intermediate flange.

#### Material:

**Entirely made of steel, fully surface-hardened.**

**Supplied with:**

Includes: 1 set of jaws, 1 chuck key, 1 set fastening screws.

**Note:**

Bore E can be bored out: Size 160 to 45 mm, size 200 to 55 mm, size 250 to 75 mm, size 315 to 102 mm (at additional charge).

Colour code for accessories: Röhm self-centring chucks and jaws

Clamping range with external hard top jaws: 8 - 253 mm

Clamping range with internal hard top jaws: 99 - 261 mm

Clamping stroke per jaw S: 8 mm

External Ø A: 256 mm

Aperture E: 62 mm

Centring taper Ø B: 139.719 mm

---

**Technical description**

Clamping range with internal hard top jaws	99 - 261 mm
Clamping range with external hard top jaws	8 - 253 mm
Centring taper Ø B	139.719 mm
Type	250
Clamping stroke per jaw S	8 mm
maximum speed	4200 min <sup>-1</sup>
Number of studs	4
Weight	33 kg
Aperture E	62 mm
Size of studs	M16
Short taper arbor	8
External Ø A	256 mm
Chuck key square socket K	14 mm
Standard	DIN 702-3
Colour code for accessories	Röhm self-centring chucks and jaws
Type of product	Self-centring chucks

---

**Accessories**


---

Hardened top jaw set, 3 pieces for chuck type 250	313210 250
Base jaw set, 3 pieces, straight teeth for chuck type 250	313207 250
Base jaw set, 3 pieces, angled serrations for chuck type 250	313205 250
Hardened top jaw set, 3 pieces for chuck type 250	313250 250
Base jaw set, 3 pieces, angled serrations for chuck type 250	313200 250