



Quick-change lathe tool post, Type: A



Order data

Order number	318000 A
GTIN	4045197315694
Item class	36A

Description

Application:

Place the lathe tool post with its surface-ground face on to the cross slide in a horizontal position and clamp it. To do this, the bore of the centring plate must have been turned beforehand. Alignment is performed with the boring bar and boring bar holder clamped in position, aligned at right angles to the face plate. Then adjust the pointer to the zero mark of the cover disc and tighten the T-bolt securely. For precision lathe work or heavy roughing cuts, it is advisable to secure the post with two dowel pins. The holes are pre-drilled.

Supplied with:

1 eccentric lever for No. 318000, 1 tool post key for No. 318100; 318200.

Technical description

Height	54 mm
maximum reach A	48 mm
maximum turning tool height h	20 mm
Type	A
Bore Ø of the centering plate	10 mm
Bore Ø of the head	20 mm

maximum cross slide width SB	100 mm
maximum drive power of lathe	1.472 kW
Width	100 mm
Type of product	Steel toolholder

Accessories

Quick-change boring bar holder Type A	318200 A
Quick-change turning toolholder Type A16/75	318100 A16/75
Clamping arm complete suitable for toolholder head A	318150 A
Quick-change turning toolholder Type A20/90	318100 A20/90
Quick-change parting-off toolholder without tool Type A	318600 A
Quick-change toolholder with plain bore Type A	318300 A
Quick-change turning toolholder Type A16/90	318100 A16/90
Quick-change turning toolholder Type A20/75	318100 A20/75