

FAHRION®
PRAZISION
Precision ER collet chuck CENTRO P, HSK-A 100 A = 160, Type CP for ER: 25

Order data

Order number	305960 25
GTIN	2050001703583
Item class	33F

Description
Version:

- **Ground externally and internally. With Balluffchip bore.**
- **Run-out and repetition accuracy 3 µm at 3×D, maximum 50 mm.**
- **Very high clamping forces due to the collet fully seated in the chuck and coated clamping nut.**
- **Vibration damping due to the element collet and mass of the chuck.**
- **Alternatively without seals, with ER clamping nut CP No. 309655 or sealed system with ER clamping nut CP for HP sealing rings No. 309665 in conjunction with HP sealing rings No.309666 – 309668 (for internal coolant supply or as a dirt trap!).**

Advantage:

Patented optimum seating of the collet, double guides, trapezoidal thread and low-friction coated clamping nut amalgamate when clamped into a sturdy unit, thus ensuring a very high degree of rigidity and precision.

Application:

For high precision clamping of tools with plain shanks.

Supplied with:

Without clamping nut and sealing rings.

Optional extras:

Precision ER collets for HP No. 309368 – 309381, and for taps No. 309402; 309419 (not Horex). ER clamping nuts CP No. 309655; 309665. HP sealing rings No. 309666 – 309668. CP roller bearing wrenches No. 309754; 309756.

Note:

- **CP chuck clamps only nominal Ø up to shank Ø tolerance h10.**
- **Use in combination with Fahrion collets.**

Machining strategy: HSC

Shape: A
Clamping range: 2 - 16 mm
External Ø D: 40 mm

Technical description

Clamping range	2 - 16 mm
Type CP for ER	25
External Ø D	40 mm
Shape	A
Series	Centro P
Adapter	HSK-A 100 A = 160
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity ER collet with CP collet chuck	≤ 6 µm
Concentricity HP collet with CP collet chuck	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

Accessories

ER collet HP with seal Nominal clamping Ø d 3 mm	309374 3
ER collet HP Nominal clamping Ø d 13 mm	309373 13
ER collet HP with seal Nominal clamping Ø d 6 mm	309374 6
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309409 12
ER collet HP Nominal clamping Ø d 9 mm	309373 9
ER collet HP with seal Nominal clamping Ø d 5 mm	309374 5
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309413 4,5

ER collet set HP (4; 6; 8; 10; 12; 14; 16mm) 430 E	309393
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309409 9
CP roller bearing wrench for torque wrenches Type 25	309756 25
ER collet HP Nominal clamping Ø d 14 mm	309373 14
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309413 7
ER collet HP Nominal clamping Ø d 12 mm	309373 12
ER collet HP with seal Nominal clamping Ø d 7 mm	309374 7
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309409 10
ER collet HP Nominal clamping Ø d 16 mm	309373 16
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309409 4,5
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309409 14
ER collet set HP with seal (4; 6; 8; 10; 12; 14; 16mm) 429 E	309394
ER collet HP with seal Nominal clamping Ø d 8 mm	309374 8
ER collet HP Nominal clamping Ø d 4 mm	309373 4
ER collet HP with seal Nominal clamping Ø d 4 mm	309374 4
ER collet HP Nominal clamping Ø d 10 mm	309373 10
ER collet HP Nominal clamping Ø d 5 mm	309373 5
ER collet HP with seal Nominal clamping Ø d 16 mm	309374 16
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 8 mm	309413 8
ER collet HP with seal Nominal clamping Ø d 15 mm	309374 15
ER collet HP with seal and spray nozzles Nominal clamping Ø d 4 mm	309375 4
ER collet HP with seal and spray nozzles Nominal clamping Ø d 8 mm	309375 8
ER collet HP Nominal clamping Ø d 2 mm	309373 2
	309413 9

ER collet for machine taps with seal and spray nozzles
Nominal clamping \varnothing d 9 mm

ER collet HP Nominal clamping \varnothing d 15 mm	309373 15
ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 12 mm	309375 12
ER collet for machine taps with seal Nominal clamping \varnothing d 6 mm	309409 6
ER collet HP with seal Nominal clamping \varnothing d 12 mm	309374 12
ER collet HP with seal Nominal clamping \varnothing d 11 mm	309374 11
ER collet HP Nominal clamping \varnothing d 3 mm	309373 3
ER collet HP with seal Nominal clamping \varnothing d 10 mm	309374 10
ER collet HP Nominal clamping \varnothing d 8 mm	309373 8
ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 14 mm	309375 14
ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 6 mm	309375 6
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 11 mm	309413 11
ER collet HP Nominal clamping \varnothing d 6 mm	309373 6
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 6 mm	309413 6
ER collet HP with seal Nominal clamping \varnothing d 13 mm	309374 13
ER collet HP with seal Nominal clamping \varnothing d 14 mm	309374 14
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 12 mm	309413 12
ER collet HP Nominal clamping \varnothing d 7 mm	309373 7
ER collet for machine taps with seal Nominal clamping \varnothing d 11 mm	309409 11
ER collet HP Nominal clamping \varnothing d 11 mm	309373 11
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 10 mm	309413 10
ER collet for machine taps with seal Nominal clamping \varnothing d 7 mm	309409 7

CP sealing ring Clamping \varnothing (1 mm increments) 2 mm	309667 2
ER collet for machine taps with seal Nominal clamping \varnothing d 8 mm	309409 8
ER collet HP with seal and spray nozzles Nominal clamping \varnothing d 10 mm	309375 10
ER collet HP with seal Nominal clamping \varnothing d 9 mm	309374 9
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 14 mm	309413 14
ER collet for machine taps with seal Nominal clamping \varnothing d 16 mm	309409 16
CP roller bearing wrench Type 25	309754 25