


Garant
Face mill arbor with cooling channel bore, HSK-F 63 A = 100, Spigot Ø d1: 40mm

Order data

Order number	306563 40
GTIN	4045197587893
Item class	31A

Description
Version:

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

With **cooling channel bores.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Special toggle spanner No. 309840.

Technical description

Spigot Ø d ₁	40 mm
Suitable toggle spanner No. 309840	40
Spare milling cutter lock screw No. 309860 / 309861	40
Milling mandrel length L ₄	27 mm

Overhang dimension A	100 mm
External Ø D	88 mm
Clamping Ø D ₁	40 mm
Adapter	HSK-F 63 A = 100
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

HSK coolant tube for HSK 40	309880 40
Socket wrench for coolant tubes for HSK 40	309890 40
Milling cutter lock screw for mandrel Ø 40 mm	309860 40
Toggle spanner for mandrel Ø 40 mm	309840 40