

EWS
Axial milling cutter spigot VARIA, V5, Spigot Ø d1: 16 mm

Order data

Order number	319841 16
GTIN	2050001077998
Item class	33E

Description
Advantage:

- **Quick change using a single clamping point, therefore tool change without risk of injury.**
- **Cutter tools lie pre-set at the machine.**
- **Compact design - low unit costs.**

Application:

With drive keyway. For milling cutters with keyways and cross slots.

Note:

Maximum tightening torque for VX3 and VX4 is 5.7 Nm, which can be achieved using the appropriate torque screwdriver No. 211750 size 5.7. Maximum tightening torque for V3, V4 and V5 is 10 Nm. When releasing the deposits, do not travel beyond the stop.

Through coolant supply on request.

Milling mandrel length L₄: 19 mm

Collar width L₅: 6 mm

Technical description

Spigot Ø d ₁	16 mm
Milling mandrel length L ₄	19 mm
Collar width L ₅	6 mm
Adapter	V5

Type of product

Milling cutter spigot