


**FAHRION®**  
FAHRENDEN PROFISSUM
**OZ collet for chuck, 2 # 16 mm, Nominal clamping  $\varnothing$  d: 16mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 309540 16     |
| GTIN         | 2050001704481 |
| Item class   | 39Y           |

**Description**
**Version:**

Spring steel, through hardened and ground. The through bore (longer clamping range than DIN collets) increases the clamping force. More slits than DIN collets, giving a greater insertion depth in the collet chuck. Suitable for jobber drills, for clamping on the guide land **Clamping range = Nominal size down to minus 0.5 mm.** 5 or 6 slits each end.

**Advantage:**

- **Better radial run-out = axially parallel centring in taper; no tumbling.**
- **Higher clamping force = due to improved grip.**
- **Higher system stiffness = suitable for high-speed milling.**
- **Longer tool life.**

**Technical description**

|                                  |           |
|----------------------------------|-----------|
| Nominal clamping $\varnothing$ d | 16 mm     |
| for chuck                        | 2 - 16 mm |
| Product name attribute           | 2 # 16 mm |
| Standard                         | ISO 10897 |
| Type                             | 415 E     |
| External $\varnothing$ D         | 25.5 mm   |

|                  |        |
|------------------|--------|
| Overall length L | 40 mm  |
| Type of product  | Collet |