

**Clamping head soft, SK 52, Initial bore Ø: 15mm****Order data**

| | |
|--------------|---------------|
| Order number | 329926 15 |
| GTIN | 2050001922632 |
| Item class | 33H |

Description**Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

| | |
|-----------------|---------------|
| Initial bore Ø | 15 mm |
| Hardness | 60 HR |
| Length L | 46 mm |
| Adapter | SK 52 |
| Type of product | Clamping head |

