

**ALZMETALL**  
 we drive productivity

**Bench drill ALZTRONIC, maximum drill Ø in steel: 12 mm**

**Order data**

Order number	076560 12
GTIN	2050001755360
Item class	03P

**Description**
**Version:**

High-speed, durable and precise bench drill.

- **AC motor 230 V, 50 Hz.**
- **Digital speed display.**
- **Stepless speed adjustment.**
- **Reversible.**
- **Swivelling spindle guard with electrical interlock.**
- **Mushroom-head pushbutton (latching) for EMERGENCY STOP.**
- **24-month warranty, 10-year spare part availability guarantee.**
- **Without drill chuck.**

With height-adjustable and swivelling drill head.

**Attention:**

German version. Order free UK adapter plug No. 08 1172\_GB.

**Note:**

Plates for other bench drills available on request.

Manufacturer's designation: ALZTRONIC 12

Power consumption: 540 W

maximum speed: 250 - 5000 rpm

Toolholder: B16

maximum machine tap Ø in steel: M10

Spindle stroke: 40 mm

## Technical description

Throat	200 mm
Distance spindle-base plate minimum	110 mm
Manufacturer's designation	ALZTRONIC 12
maximum machine tap $\varnothing$ in steel	M10
Column $\varnothing$	50 mm
Power consumption	540 W
maximum drill $\varnothing$ in steel	12 mm
Weight	64 kg
Toolholder	B16
maximum speed	250 - 5000 rpm
Machine baseplate width of usable area	300 mm
Machine baseplate height of usable area	240 mm
Feed	manual
Drill head height adjustment	Handwheel
Spindle stroke	40 mm
Distance spindle-base plate maximum	250 mm
T-slot nominal size	12 mm
Number of T-slots	2
T-slot pitch	80 mm