



High-performance cutting oil high-viscosity, chlorine-free DAR 50 Visco, Contents: 0,5l



Order data

Order number	084220 0,5
GTIN	2050000966217
Item class	08J

Description

Version:

Cutting oil for the most demanding applications. Recommended for mixing with normal mineral-based cutting oil (but not with water-soluble oils).

Application by brush, spray can, spray bottle or lubrication system.

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching and sawing) and also for **forming**. Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys. Ideal for **non-ferrous metals**.

High viscosity product based on mineral oil, very well suited for thread tapping, good adherence.

Technical description

Kinematic viscosity	174 mm ² /s
Version	Spray bottle
Flashpoint	180 °C
Colour	brown
Storage temperature	5 - 40 °C
Contents	0.5 l
Type of product	Cutting oil / grinding oil