

FAHRION®
FAHRENDEN PROFISSION
OZ collet for chuck, 2 # 25 mm, Nominal clamping \varnothing d: 10mm

Order data

| | |
|--------------|---------------|
| Order number | 309550 10 |
| GTIN | 2050001704559 |
| Item class | 39Y |

Description
Version:

Spring steel, through hardened and ground. The through bore (longer clamping range than DIN collets) increases the clamping force. More slits than DIN collets, giving a greater insertion depth in the collet chuck. Suitable for jobber drills, for clamping on the guide land **Clamping range = Nominal size down to minus 0.5 mm.** 5 or 6 slits each end.

Advantage:

- **Better radial run-out = axially parallel centring in taper; no tumbling.**
- **Higher clamping force = due to improved grip.**
- **Higher system stiffness = suitable for high-speed milling.**
- **Longer tool life.**

Technical description

| | |
|----------------------------------|-----------|
| Nominal clamping \varnothing d | 10 mm |
| for chuck | 2 - 25 mm |
| Product name attribute | 2 # 25 mm |
| Standard | ISO 10897 |
| Type | 462 E |
| External \varnothing D | 35.05 mm |

| | |
|------------------|--------|
| Overall length L | 52 mm |
| Type of product | Collet |