



Top jaws set, 3 pieces, for chuck type: 315



Order data

Order number	313750 315
GTIN	4019208193786
Item class	33R

Description

Version:

Bevelled for small clamping \emptyset .

Precision milled slots and serration, **burnished**.

Soft top jaws, long, serration $1.5 \times 60^\circ$.

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, RöhM and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

for thread DIN 912	M14
Slot width D	18 mm
Width B	50 mm
Length L	145 mm
Hole centre spacing a	30 mm
Bore spacing b	30 mm

Height H	50 mm
for chuck type	315 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws