

**Flow drilling set - standard including fluteless taps, for thread M: M6-M10****Order data**

Order number	082721 M6-M10
GTIN	2050001740076
Item class	04D

Description**Description:**

The polygon contour of the carbide flow drill generates frictional heat which plasticises all types of metal materials. This allows closed apertures to be created in a variety of thicknesses of materials, without chips, in just a few seconds.

Advantage:

- **Large savings of time and costs compared to conventional processes (such as drawn-on nuts).**
- **Generates no chips or swarf; supersedes rivet nuts, weld nuts and press nuts.**
- **Solid basis for threads with high pull-out forces.**
- **For all popular material thicknesses and thread sizes (threads to DIN 13).**

Content:

1 each flowdrill and fluteless tap: Size M6; M8; M10

Note:

Other versions and sets for special applications (such as for thin sheet metal) available on request. **For suitable fluteless taps see items No. 139115 ff.**

Technical description

for thread M	M6-M10
Type of product	Flow drills

Accessories

Flow drill - standard (with collar) for thread M M8	082730 M8
Flow drill - standard (with collar) for thread M M6	082730 M6
Flow drill - standard (with collar) for thread M M10	082730 M10