

**OZ collet set type 462 E 15 pieces, for chucks 5–25 mm****Order data**

Order number	309562
GTIN	2050001699404
Item class	39Z

Description**Version:**

Spring steel, through hardened and ground. The through bore (longer clamping range than DIN collets) increases the clamping force. More slits than DIN collets, giving a greater insertion depth in the collet chuck. Suitable for jobber drills, for clamping on the guide land **Clamping range = Nominal size down to minus 0.5 mm.** 5 or 6 slits each end.

Advantage:

- **Better radial run-out = axially parallel centring in taper; no tumbling.**
- **Higher clamping force = due to improved grip.**
- **Higher system stiffness = suitable for high-speed milling.**
- **Longer tool life.**

Supplied with:

OZ collets (No. 309550) Ø 5–16 mm (in 1 mm increments) and Ø 18, 20, and 25 mm, in a wooden box.

Standard: ISO 10897

Technical description

Standard	ISO 10897
Type of product	Clamping head

