

Garant
**Shrink-fit chucks with cooling channel bore, HSK-A 100 short, Clamping range
 Ø D1: 25mm**

Order data

Order number	308277 25
GTIN	4045197291455
Item class	31A

Description
Version:

Integral length adjustment of the tool from clamping Ø D₁ 6 mm (adjustment travel 10 mm).
 From clamping Ø D₁ 6 mm with tapped holes for balancing screws.

- **High-temperature steel.**
- **Sizes 3 – 5 for carbide, from size 6 for HSS and carbide.**
- **With RFID/Balluffchip bore.**

GARANT: HSK mating faces machined. **All shanks hard turned (for smooth running!).**

With **cooling channel bores** tapped for plugging.

Application:

- **For holding end mills and drills with parallel shank to h6 tolerance.**
- **Suitable for inductive, contact and hot air shrink-fit units.**

Supplied with:

For chucks with length adjustment including a length adjustment screw (from clamping Ø D₁ 6 mm).

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, shrink-fit chuck extension No. 302410 – 302416, shrink-fit units No. 354210 – 354450, balancing screw set No. 309906 180.

Technical description

Overhang dimension A	115 mm
Clamping Ø D ₁	25 mm

Ø D ₂	44 mm
External Ø D	53 mm
Cooling channel bore	lockable
Adapter	HSK-A 100 short
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Shrink-fit chuck

Accessories

Shrink-fit unit Type SU1	354210 SU1
Screening plate for coilSU1 for clamping Ø 20-32 mm	354240 20-32
Cooling adapter short4.5° for clamping Ø 22,1-32 mm	354235 22,1-32
Cooling adapter long4.5° for clamping Ø 22,1-32 mm	354236 22,1-32
Cooling unit Type CU1	354215 CU1
Subframe cupboard	354290