



## Top jaw set, 4 pieces, soft, for chuck type: 350 mm



### Order data

Order number	314500 350
GTIN	4019208034331
Item class	36R

### Description

#### Version:

**Precision milled** contact face, **not burnished**.

#### Application:

For fitting to hardened base jaws.

#### Material:

16 MnCr5

#### Suitable for :

**Four-jaw lathe chucks No. 312000; 312500; 312700.**

#### Note:

- **Jaws can generally be renewed in the chuck as long as the guide in the body is not worn out.**
- **Top, turning, and drilling jaws bought subsequently must be ground in the chuck for radial and axial run-out.**

Aluminium top jaws **on request**.

suitable for colour code: Röhm geared scroll chucks and jaws

Length L: 137 mm

Height H: 63 mm

Slot width D: 12.72 mm

Bore spacing b: 76.2 mm

Tenon length A: 19.02 mm

also suitable for chuck type: 400 mm

### Technical description

Length L	137 mm
----------	--------

Height H	63 mm
Bore spacing b	76.2 mm
for chuck type	350 mm
also suitable for chuck type	400 mm
Tenon length A	19.02 mm
Slot width D	12.72 mm
suitable for colour code	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chuck jaws