



High-performance cutting oil chlorine-free Alpha 93, Contents: 0,3l



Order data

Order number	084210 0,3
GTIN	2050000966040
Item class	08J

Description

Version:

Cutting oil for the most demanding applications. Recommended for mixing with normal mineral-based cutting oil (but not with water-soluble oils).

Application by brush, spray can, spray bottle or lubrication system.

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching and sawing) and also for **forming**. Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys. Ideal for **non-ferrous metals**.

Ideal when minimum lubrication is required, due to being free of mineral oil.

Technical description

Labelling of hazardous substances	GHS02: Flame
Version	Spray can

Boiling point	-44 °C
hazardous goods class	2.1
Spray head	Standard
Colour	pale yellow
Spontaneous ignition temperature	365 °C
Storage temperature	15 - 35 °C
Contents	0.3 l
Type of product	Cutting oil / grinding oil