

 Mahr**Digital caliper with data output, Measuring range: 300mm****Order data**

Order number	412729 300
GTIN	4059192002183
Item class	43A

Description**Version:**

Easy-to-read, high-contrast LCD display with 8.5 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. Without depth gauge.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498940.

Technical description

Jaw length	64 mm
Calibration	A1
Working time	approx. 3 years
Reversible reading	mm / inch
Digit height LCD display	8.5 mm
Standard	ISO 13385
Depth gauge available	no
Scale divisions	0.01 mm

Scale divisions	0.0005 in
Measuring range	0 - 300 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.04 mm
Interface	RS232C interface
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Multi-receiver / USB keyboard interface Type	498975
Connection cablesimplex with data key Type D2	498940 D2
Receiver / USB keyboard interface Type	498965
Connection cablesimplex with data key Type R2	498940 R2
Button cell / special battery Battery type CR2032	081560 CR2032
Plastic case Type MS300	412470 MS300

Connection cablesimplex with data key Type USB2	498940 USB2
Transmitter Type S4E	498966 S4E