

**Universal laser “autoMAGIC”, Type: 5SP****Order data**

|              |               |
|--------------|---------------|
| Order number | 468465 5SP    |
| GTIN         | 4007368102946 |
| Item class   | 46O           |

**Description****Version:**

Cross-hairs and 5-beam laser combined in a single device, **self-levelling via a magnetically damped pendulum system**. Pulsed laser lines horizontal and vertical, can be adjusted separately or jointly. Plumb-line lasers upwards and downwards; 3 horizontal laser beams forwards, to the left, and to the right; all laser beams are at an 90° angle to each other. Lockable for generating “oblique lines” and for protection during transport.

**Supplied with:**

Magnetic wall bracket with threads for attachment to stands, laser target board, carrying case, and 3 batteries No. 081561 size LR6.

**Technical description**

|                 |            |
|-----------------|------------|
| Height          | 112 mm     |
| Laser class     | 2M         |
| Weight          | 0.5 kg     |
| Width           | 116 mm     |
| Levelling range | ±3 degrees |

|   |                     |
|---|---------------------|
| Depth   | 69 mm               |
| Range   | 30 m                |
| Threaded socket for stand                               | 1/4 UNC, 5/8 UNC in |
| Manufacturer's designation                              | 654KLP5SP           |
| Number of batteries contained                           | 3                   |
| Article no of the battery / rechargeable battery fitted | 081561 LR6          |
| Power supply  | Battery-powered     |
| Calibration   | Price on request    |
| Type of product   | Universal laser     |

---

## Accessories

|   |            |
|---|------------|
| Photography tripod Type                             | 468558     |
| Alkaline-manganese batteries International size LR6 | 081561 LR6 |