

Garant
Base extension with safety slip clutch, M3 – 12, Tap shank Ø: 8mm

Order data

Order number	335645 8
GTIN	4045197554048
Item class	31M

Description
Version:

Rigid quick-change tapping collets **without** safety clutch.

Application:

For GARANT intermediate sections No. 338140 – 338142.

Note:

Inserts with slip clutch are supplied with the torque setting for machining steel (R_m 600 – 800 N/mm²). The setting can be modified as required by adjusting the nut.

Technical description

Tap shank Ø	8 mm
Shank square	6.2 mm
Tapping range	M3 – 12
External Ø D	32 mm
Shank Ø d	19 mm
Connection length L	21.5 mm
Overhang length H	70 mm
Ø e	23 mm
Type of product	Extension

