



## Precision small dial indicator shock-resistant, Measuring range / Body Ø: 5/40 mm



### Order data

Order number

432505 5/40

GTIN

4045197199591

Item class

42C

### Description

#### Version:

Precision small dial indicators with strong metal casing, clamping shank  $\varnothing$  8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial.

Shock-resistant.

Dimensions to DIN EN ISO 463, issue June 2006.

#### Optional extras:

Special contact points No. 434900; 434910; 434915.

Packaging: sturdy box

Standard: DIN 878

Calibration: C1

Graduation: 0.01 mm

Reading per pointer revolution: 1 mm

Gauging force: 0.6 - 1 N

### Technical description

Reading per pointer revolution

1 mm

Gauging force	0.6 - 1 N
Calibration	C1
Graduation	0.01 mm
Body Ø	40 mm
Measuring range	5 mm
Standard	DIN 878
Measurement technology	analogue
Packaging	sturdy box
Type of product	Dial Indicator

## Services

Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	013210 10
Labelling laser-etched Type	018940
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	013250 12,5

## Accessories

Steel contact point Type 2	434900 2
Ruby contact point Type 2	434915 2
Carbide contact point Type 2	434910 2
Steel contact point Type 10	434900 10
Steel contact point Type 11	434900 11
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 11/20	434900 11/20
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 12	434900 12
Steel contact point Type 13	434900 13

Steel contact point Type 14	434900 14
Steel contact point Type 14/15	434900 14/15
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 15	434900 15
Steel contact point Type 16	434900 16
Steel contact point Type 17	434900 17
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 18/3	434900 18/3
Steel contact point Type 18/4	434900 18/4
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 18/6	434900 18/6
Steel contact point Type 19/10	434900 19/10
Steel contact point Type 19/11	434900 19/11
Steel contact point Type 19/7	434900 19/7
Steel contact point Type 19/8	434900 19/8
Steel contact point Type 19/9	434900 19/9
Steel contact point Type 20	434900 20
Steel contact point Type 24	434900 24
Steel contact point Type 28	434900 28
Steel contact point Type 29/10	434900 29/10
Steel contact point Type 29/20	434900 29/20
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 32	434900 32
Steel contact point Type 39	434900 39
Steel contact point Type 40/10	434900 40/10
Steel contact point Type 40/7,8	434900 40/7,8

Carbide contact point Type 10	434910 10
Carbide contact point Type 11	434910 11
Carbide contact point Type 14	434910 14
Carbide contact point Type 16	434910 16
Carbide contact point Type 17	434910 17
Carbide contact point Type 18/1	434910 18/1
Carbide contact point Type 18/2	434910 18/2
Carbide contact point Type 18/3	434910 18/3
Carbide contact point Type 18/4	434910 18/4
Carbide contact point Type 18/5	434910 18/5
Carbide contact point Type 18/6	434910 18/6