



Dial indicator, Measuring range / Body Ø: 10/58mm



Order data

Order number	431980 10/58
GTIN	4045197204165
Item class	42C

Description

Version:

Dimensions to DIN EN ISO 463, issue June 2006. Precision dial indicators with metal housing, clamping shank Ø 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial. Central pointer for 1/100 mm reading, small pointer on sub-scale for 1 mm reading. Outer ring with 2 adjustable tolerance pointers.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Graduation	0.01 mm
Measuring range	10 mm
Gauging force	0.4 - 1.4 N
Calibration	C1
Reading per pointer revolution	1 mm
Body Ø	58 mm

Standard	DIN 878
Measurement variation MPE (measurement range)	15 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/431980-10/58>