



Precision dial indicator shock-resistant, Measuring range / Body Ø: 5/58mm



Order data

| | |
|--------------|---------------|
| Order number | 433400 5/58 |
| GTIN | 4031452100563 |
| Item class | 46C |

Description

Version:

Strong, satin chrome plated brass casing; unbreakable dial glass.

Clamping shank Ø 8 mm h6, hardened and ground.

High accuracy version.

The most important parts of the mechanism are **jewel-mounted**.

Central pointer **for 1/1000 mm reading**.

Outer ring of dial face can be rotated to zero the dial.

Nearly constant measuring force over the entire measuring range.

High-quality shock absorption for particularly long working life.

Dimensions to DIN EN ISO 463, issue June 2006.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

| | |
|--------------------------------|----------|
| Reading per pointer revolution | 0.2 mm |
| Graduation | 0.001 mm |

| | |
|---|-------------------------|
| Body Ø | 58 mm |
| Measuring range | 5 mm |
| Calibration | C2 |
| Gauging force | 1.5 - 2 N |
| Standard | Manufacturer's standard |
| Measurement variation MPE (measurement range) | 10 µm |
| Measurement technology | analogue |
| Packaging | sturdy box |
| Type of product | dial gauge |

Services

| | |
|---|-------------|
| CalibrationDial indicator, analogue 0.001 maximum measuring span 5 mm | 023020 5 |
| DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm | 023010 12,5 |

Accessories

| | |
|--|--------------|
| Carbide contact point Type 2 | 434910 2 |
| Extension for contact points Length L 90 mm | 434920 90 |
| Extension for contact points Length L 20 mm | 434920 20 |
| Extension for contact points Length L 15 mm | 434920 15 |
| Carbide contact point Type 14 | 434910 14 |
| Carbide contact point Type 10 | 434910 10 |
| Steel contact point Type 11/25 | 434900 11/25 |
| Angled bracket for dial indicator60° Clamping length 25 mm | 434918 25 |
| Carbide contact point Type 16 | 434910 16 |
| Steel contact point Type 14/15 | 434900 14/15 |
| Steel contact point Type 14/40 | 434900 14/40 |
| Steel contact point Type 29/20 | 434900 29/20 |

| | |
|---|--------------|
| Steel contact point Type 11/35 | 434900 11/35 |
| Magnetic rear panel for dial indicators for body Ø 58 mm | 434835 58 |
| Outer ring for dial indicator Type 58 | 432020 58 |
| Steel contact point Type 39 | 434900 39 |
| Steel contact point Type 11/20 | 434900 11/20 |
| Steel contact point Type 15 | 434900 15 |
| Steel contact point Type 29/10 | 434900 29/10 |
| Dial indicator glass Type 58 | 432010 58 |
| Steel contact point Type 30/10 | 434900 30/10 |
| Carbide contact point Type 18/5 | 434910 18/5 |
| Extension for contact points Length L 40 mm | 434920 40 |
| Steel contact point Type 14 | 434900 14 |
| Steel contact point Type 18/4 | 434900 18/4 |
| Steel contact point Type 14/20 | 434900 14/20 |
| Extension for contact points Length L 30 mm | 434920 30 |
| Steel contact point Type 14/30 | 434900 14/30 |
| Steel contact point Type 2 | 434900 2 |
| Carbide contact point Type 18/6 | 434910 18/6 |
| Steel contact point Type 28 | 434900 28 |
| Steel contact point Type 24 | 434900 24 |
| Ruby contact point Type 2 | 434915 2 |
| Steel contact point Type 18/3 | 434900 18/3 |
| Angled bracket for dial indicator 45° Clamping length 25 mm | 434917 25 |
| Carbide contact point Type 18/3 | 434910 18/3 |
| Extension for contact points Length L 100 mm | 434920 100 |
| Carbide contact point Type 17 | 434910 17 |
| Steel contact point Type 10 | 434900 10 |
| Carbide contact point Type 18/4 | 434910 18/4 |
| Steel contact point Type 16 | 434900 16 |

| | |
|---|--------------|
| Steel contact point Type 13 | 434900 13 |
| Carbide contact point Type 11 | 434910 11 |
| Steel contact point Type 11 | 434900 11 |
| Angled bracket for dial indicator 60° Clamping length 50 mm | 434918 50 |
| Carbide contact point Type 18/2 | 434910 18/2 |
| Steel contact point Type 18/6 | 434900 18/6 |
| Steel contact point Type 18/1 | 434900 18/1 |
| Extension for contact points Length L 70 mm | 434920 70 |
| Steel contact point Type 17 | 434900 17 |
| Steel contact point Type 20 | 434900 20 |
| Pivoting contact point | 434912 |
| Steel contact point Type 11/15 | 434900 11/15 |
| Steel contact point Type 11/30 | 434900 11/30 |
| Extension for contact points Length L 50 mm | 434920 50 |
| Steel contact point Type 18/5 | 434900 18/5 |
| Extension for contact points Length L 80 mm | 434920 80 |
| Extension for contact points Length L 60 mm | 434920 60 |
| Steel contact point Type 18/2 | 434900 18/2 |
| Angled bracket for dial indicator 45° Clamping length 50 mm | 434917 50 |
| Carbide contact point Type 18/1 | 434910 18/1 |
| Extension for contact points Length L 10 mm | 434920 10 |
| Steel contact point Type 12 | 434900 12 |