



## Special pull stud with no internal thread sealed, with bore, suitable for steep tapers: 40



### Order data

Order number	308720 40
GTIN	4045197151049
Item class	32Z

### Description

#### Description:

The toolholder is securely pulled into the spindle by the spindle's clamping gripper using the pull stud. Pull studs come in different versions. They are an important link between the machine and tool. Stringent requirements apply for the accuracy, strength and reliability of pull studs.

#### Application:

For tools with taper shanks see also **DIN 69871 / ISO 7388-1**.

#### Note:

Look in the eShop – you will find the right clamping wrench and width for every job.  
When installing the pull stud, cheque the correct tightening torque. **Sealed** – with O-ring.  
No suitable chuck key available.

Collar Ø D: 25.1 mm

Head Ø D<sub>1</sub>: 21.1 mm

Overall length L: 53 mm

L<sub>1</sub>: 25.1 mm

Thread M: M16

maximum tightening torque: 50 N·m

### Technical description

Thread M	M16
suitable for taper arbors with colour code	SK 40
suitable for steep tapers	40

maximum tightening torque	50 N·m
Collar Ø D	25.1 mm
Head Ø D <sub>1</sub>	21.1 mm
L <sub>1</sub>	25.1 mm
Overall length L	53 mm
Width across flats	22 mm
Hole characteristics	with bore
Type of product	Pull Stud