



## Precision small dial indicator, Measuring range / Body Ø: 3/32mm



### Order data

Order number	432500 3/32
GTIN	4031452100136
Item class	46C

### Description

#### Version:

Precision small dial indicators with strong metal casing, clamping shank  $\varnothing$  8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial.

Dimensions to DIN EN ISO 463, issue June 2006.

#### Optional extras:

Special contact points No. 434900; 434910; 434915.

### Technical description

Graduation	0.01 mm
Reading per pointer revolution	0.5 mm
Body $\varnothing$	32 mm
Gauging force	0.8 - 1.2 N
Measuring range	3 mm
Calibration	C1

Standard	DIN 878
Measurement variation MPE (measurement range)	10 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

## Services

DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 3 mm	023000 3

## Accessories

Steel contact point Type 13	434900 13
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 11	434900 11
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 15	434900 15
Carbide contact point Type 18/6	434910 18/6
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Extension for contact points Length L 50 mm	434920 50
Carbide contact point Type 18/1	434910 18/1
Carbide contact point Type 14	434910 14
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 18/1	434900 18/1
Carbide contact point Type 11	434910 11
Carbide contact point Type 18/3	434910 18/3
Angled bracket for dial indicator 60° Clamping length 25 mm	434918 25

Steel contact point Type 29/20	434900 29/20
Ruby contact point Type 2	434915 2
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 10	434900 10
Steel contact point Type 12	434900 12
Extension for contact points Length L 80 mm	434920 80
Carbide contact point Type 16	434910 16
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 11/15	434900 11/15
Carbide contact point Type 10	434910 10
Carbide contact point Type 17	434910 17
Extension for contact points Length L 70 mm	434920 70
Extension for contact points Length L 10 mm	434920 10
Steel contact point Type 18/4	434900 18/4
Extension for contact points Length L 15 mm	434920 15
Steel contact point Type 11/20	434900 11/20
Angled bracket for dial indicator 45° Clamping length 25 mm	434917 25
Steel contact point Type 24	434900 24
Steel contact point Type 28	434900 28
Angled bracket for dial indicator 45° Clamping length 50 mm	434917 50
Extension for contact points Length L 90 mm	434920 90
Extension for contact points Length L 100 mm	434920 100
Steel contact point Type 18/3	434900 18/3
Steel contact point Type 20	434900 20
Pivoting contact point	434912
Steel contact point Type 14/15	434900 14/15
Carbide contact point Type 2	434910 2
Steel contact point Type 14	434900 14

Steel contact point Type 18/6	434900 18/6
Steel contact point Type 16	434900 16
Steel contact point Type 11/25	434900 11/25
Extension for contact points Length L 30 mm	434920 30
Steel contact point Type 17	434900 17
Steel contact point Type 2	434900 2
Steel contact point Type 11/35	434900 11/35
Extension for contact points Length L 20 mm	434920 20
Extension for contact points Length L 60 mm	434920 60
Steel contact point Type 29/10	434900 29/10
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 39	434900 39
Steel contact point Type 14/40	434900 14/40
Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 14/30	434900 14/30
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 30/10	434900 30/10