



## Special pull stud with internal thread, with bore, suitable for steep tapers: 40



### Order data

|              |               |
|--------------|---------------|
| Order number | 308740 40     |
| GTIN         | 4045197151063 |
| Item class   | 32Z           |

### Description

#### Description:

The toolholder is securely pulled into the spindle by the spindle's clamping gripper using the pull stud. Pull studs come in different versions. They are an important link between the machine and tool. Stringent requirements apply for the accuracy, strength and reliability of pull studs.

#### Application:

For tools with taper shanks see also **DIN 69871 / ISO 7388-1**.

#### Note:

**Sealed** – with O-ring.

Look in the eShop – you will find the right clamping wrench and width for every job.

When installing the pull stud, cheque the correct tightening torque. No suitable chuck key available.

### Technical description

|  |         |
|--|---------|
| Internal thread                            | M16     |
| suitable for taper arbors with colour code | SK 40   |
| Head Ø D <sub>1</sub>                      | 21.1 mm |
| Thread M                                   | M16     |
| suitable for steep tapers                  | 40      |
| L <sub>1</sub>                             | 25.1 mm |
| Collar Ø D                                 | 25.1 mm |

|                           |           |
|---------------------------|-----------|
| Overall length L          | 53 mm     |
| maximum tightening torque | 50 Nm     |
| Internal thread depth     | 17 mm     |
| Width across flats        | 22 mm     |
| Hole characteristics      | with bore |
| Type of product           | Pull Stud |