

**Quick-release vice for one-hand use, Jaw width A: 110mm****Order data**

Order number	365023 110
GTIN	4045197563200
Item class	32P

Description**Version:**

- **Quick adjustment of the movable jaws.**
- **Jaws through hardened and ground.**
- **Time-consuming cranking not necessary.**
- **Precise clamping due to long flat guide.**
- **Clamping of component with just one hand.**
- **One jaw with horizontal and vertical prismatic profiles for round material, one jaw smooth.**
- **Both jaws are stepped at the top to clamp flat parts.**
- **With two side support faces.**
- **Positive locking.**

Application:

For quick clamping of components on drilling machines and measuring machines.

Material:

Body and movable jaw made of sturdy special cast iron.

Accuracy:

Within **0.03 mm**.

Technical description

Colour code for suitable accessories	BM vice, blue
Overall height c	82 mm
Weight	9.5 kg

maximum overall length L ₄	510 mm
Jaw width A	110 mm
Clamping range b	130 mm
Jaw height C	32 mm
Base body width B	112 mm
Base body length a	280 mm
Type of product	Drilling machine vice

Accessories

Backstop Type 1	365028 1
Slide for No. 365023	365025