

Garant**Self-tightening drill chuck with diamond-coated jaws, Type: 130****Order data**

Order number	341050 130
GTIN	4045197191564
Item class	31K

Description**Version:**

With **diamond-coated jaws**, self-tightening.

Application:

Especially suitable **for clamping solid carbide drills** (Group 12) and for **drills with hard shanks**. For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:

DIN 238

Note:

Use high precision straight shank drill chuck arbors No. 342600.

Technical description

largest drill chuck taper \varnothing	15.733 mm
Drill head length closed	103 mm
Drill chuck taper	B 16
Type	130
Clamping range	1 - 13 mm
Drill head length open	91 mm
External \varnothing	50 mm

Type of product

Drill chuck keyless