



## Digital hand-held tachometer



### Order data

Order number	471100
GTIN	4029547006302
Item class	47B

### Description

#### Version:

Non-contact measurement by reflector strip, contact measuring by means of mechanical adapter tip, memory selectable using MODE button for maximum value, minimum value, or most recent value. Switches off automatically 30 seconds after the last key action.

#### Application:

##### Rotational speed measurement:

- optically 1 to 99,999 rpm non-contact,
- mechanically 0.1 to 19,999 rpm with contact tip.

##### Speed measurement (with measuring wheel).

- 0.10 to 1999 m/min

##### Length measurement (with measuring wheel).

- 0.02 bis 99999 m

#### Supplied with:

Includes mechanical adapter, measuring wheel (0.1 m) No. 471180, hollow measuring tip No. 471190, drive cone centre No. 471170, measuring wheel (6 inch), reflector strips No. 471150, case, 2 batteries No. 081561 size LR6.

Reversible reading: mm / inch

Error limit: 0.02 ( $\pm 1$  digit) %

Measurement distance (for optical measurement): 600 mm

Operating temperature: 0 - 50 °C

Storage temperature: -20 - 70 °C

## Technical description

Measurement distance (for optical measurement)	600 mm
Speed measuring range (optical)	0 - 99999 min <sup>-1</sup>
Operating temperature	0 - 50 °C
Storage temperature	-20 - 70 °C
Error limit	0.02 (±1 digit) %
Article no of the battery / rechargeable battery fitted	081561 LR6
Number of batteries contained	2
Power supply	Battery-powered
Reversible reading	mm / inch
Measurement technology	digital
Type of product	Hand-held tachometer

## Services

Labelling laser-etched Type	018940
-----------------------------	--------

## Accessories

Drive cone centre	471170
Drive surface disc circumference 6 inches	471181
Alkaline-manganese batteries International size LR6	081556 LR6
Reflector strip set 5 pieces	471150
Hollow measuring tip	471190
Drive surface disc circumference 100 mm	471180
Alkaline-manganese batteries International size LR6	081561 LR6