

ALLURIS

Precision hand-held tachometer, Type: CL



Order data

Order number	471300 CL
GTIN	4260244680239
Item class	47F

Description

Version:

Precision hand-held tachometer in **sturdy die-cast aluminium casing**. Large digital display, easy to use. Lengths and speeds in selectable international units. **Laser hand-held tachometer** for non-contact measurements at distances up to 4 m. **Also for contact measurements** using multi-impulse adapter (included).

Application:

Rotational speed measurement: 0.1 – 99999 rpm (mechanically up to 25,000 rpm).

Speed: 0.1– 3810 m/min

Length measurement: 0.0– 99999 m/min

Counting: 0– 99999

Supplied with:

Includes 2 measuring tips, 6 inch measuring wheel, female centre, extension shaft, operating instructions, protective case, 2 batteries No. 081561 size LR6. Additionally with screw-in adapter and reflector strips.

Optional extras:

Reflector strips No. 471315.

Technical description

Measurement distance (for optical measurement)	150 – 1500 , maximum 4000 mm
Impulses per revolution (contact measurement)	8 (with adapter)
Measurement time	1 s

Surface disc circumference	6 in
Error limit	0.006 (± 0.5 digit) %
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR6
Power supply	Battery-powered
Measurement technology	digital
Calibration	I2
Type of product	Hand-held tachometer

Services

CalibrationTachometer / stroboscope Type D	027900 D
DAkkS calibrationRotational speed sensor Type D	027910 D

Accessories

Reflector strip set35 pieces	471315
------------------------------	--------