

**Straight shank drill chuck arbor, Shank Ø / drill chuck taper: 10/10mm****Order data**

Order number	342300 10/10
GTIN	4045197294395
Item class	32X

**Description****Version:**

**Through hardened and ground.** High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

High precision version with plain shank.

**Application:**

For mounting drill chucks on to milling machines, automatic system etc. The plain shank can be clamped in a **collet or in a milling chuck**.

**Standard:**

Bohrfutterkegel **DIN 238**.

**Technical description**

Drill chuck taper DIN 238	B 10
Taper Ø D	10.094 mm
Plain shank length	40 mm
Shank Ø	10 mm
Type of product	Drill chuck adapter