



Solid lathe centre with carbide insert, Morse taper: 3



Order data

Order number	323600 3
GTIN	4045197296689
Item class	32L

Description

Version:

Point angle 60°, surfaces ground.

Full point with deep inserted **carbide centre**.

The carbide tipped lathe centres are marked with a groove to indicate maximum regrinding allowance.

Description:

Lathe centres are mainly used on lathes to support long and slim workpieces, since with these workpieces there would otherwise be a risk of the workpiece bending or moving around as a result of the forces generated.

The lathe centre is secured with a Morse taper. The workpiece is clamped in the chuck and a counterbore is added using a centre drill. After re-clamping, the lathe centre is then inserted.

Standard:

DIN 806

External Ø D: 24.1 mm

Overall length L: 125 mm

Carbide Ø H: 11 mm

Face length L₁: 38 mm

Face-point distance b: 3 mm

Technical description

Face length L ₁	38 mm
Morse taper	3
External Ø D	24.1 mm
Carbide Ø H	11 mm

Face-point distance b	3 mm
Overall length L	125 mm
Type of product	Centring drill