

 Mahr**Precision dial comparator, \pm measuring range / reading: 250/10 μ m****Order data**

Order number	434674 250/10
GTIN	4059192014025
Item class	43A

Description**Version:**

Sapphire mounted, all-in-one mechanism, particularly robust for use in the manufacturing area.

Low hysteresis due to virtually play-free gauging pins on ball guides.

Resistant to lateral forces.

One-piece housing for maximum stability and accuracy.

Shock resistance due to transmission lever which lifts up in the event of overload

Constant measuring force by straight spring.

Large overrun for convenient insertion of the component. Lifting key or lifting cable (special accessories) can be connected.

Clearly legible scale.

2 Tolerance pointers for presetting the permitted tolerance range.

Callout:**Tolerance pointers****Connection**

for foot switch No. 434930

Fine adjustment

lockable (zero setting).

Application:

As a dial bore gauge for series and individual inspections.

Optional extras:

Lifting cable No. 434930.

Technical description

Free stroke	2.5 mm
Calibration	C3
Clamping shank \varnothing h6	8 mm
Gauging force	1 N
Width	63 mm
\pm measuring range	250 μ m
Scale divisions	10 μ m
Length	95 mm
Height	20 mm
Standard	Works standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	Precision dial comparators

Services

Calibration Precision dial comparator Type FZ	023180 FZ
DAkkS calibration Precision dial comparator Type FZ	023190 FZ

Accessories

Steel contact point Type 18/2	434900 18/2
Extension for contact points Length L 50 mm	434920 50
Steel contact point Type 11/15	434900 11/15
Steel contact point Type 18/4	434900 18/4
Extension for contact points Length L 60 mm	434920 60

Steel contact point Type 24	434900 24
Lifting cables Length 140 mm	434930 140
Extension for contact points Length L 100 mm	434920 100
Extension for contact points Length L 20 mm	434920 20
Carbide contact point Type 18/2	434910 18/2
Carbide contact point Type 18/5	434910 18/5
Carbide contact point Type 2	434910 2
Angled bracket for dial indicator60° Clamping length 25 mm	434918 25
Extension for contact points Length L 80 mm	434920 80
Steel contact point Type 18/6	434900 18/6
Steel contact point Type 11/20	434900 11/20
Extension for contact points Length L 90 mm	434920 90
Carbide contact point Type 18/6	434910 18/6
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 29/20	434900 29/20
Pivoting contact point	434912
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 14/30	434900 14/30
Carbide contact point Type 18/1	434910 18/1
Ruby contact point Type 2	434915 2
Carbide contact point Type 17	434910 17
Steel contact point Type 29/10	434900 29/10
Angled bracket for dial indicator60° Clamping length 50 mm	434918 50
Steel contact point Type 11/25	434900 11/25
Carbide contact point Type 10	434910 10
Steel contact point Type 18/3	434900 18/3
Steel contact point Type 14/20	434900 14/20

Steel contact point Type 13	434900 13
Extension for contact points Length L 70 mm	434920 70
Steel contact point Type 14	434900 14
Carbide contact point Type 16	434910 16
Steel contact point Type 14/15	434900 14/15
Extension for contact points Length L 10 mm	434920 10
Steel contact point Type 11	434900 11
Steel contact point Type 12	434900 12
Steel contact point Type 39	434900 39
Lifting cables Length 500 mm	434930 500
Carbide contact point Type 14	434910 14
Extension for contact points Length L 30 mm	434920 30
Steel contact point Type 17	434900 17
Steel contact point Type 28	434900 28
Angled bracket for dial indicator45° Clamping length 50 mm	434917 50
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 15	434900 15
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 2	434900 2
Angled bracket for dial indicator45° Clamping length 25 mm	434917 25
Steel contact point Type 11/35	434900 11/35
Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 20	434900 20
Extension for contact points Length L 15 mm	434920 15
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 16	434900 16
Carbide contact point Type 11	434910 11
Carbide contact point Type 18/3	434910 18/3

Steel contact point Type 10

434900 10