

Garant
SNMG 120412, Grade: HB7140-1


Order data

Order number	251226 HB7140-1
GTIN	4045197820655
Item class	21G

Description

SNMG 120412 HB7140-1 Corner radius: 1.2 mm
 Grade: HB7140-1
 Chip breaker: VM
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 60 - 230 m/min

Technical description

Chip breaker	VM
Grade	HB7140-1
Corner radius	1.2 mm
Cutting speed v_c main application	60 - 230 m/min
Cutting depth a_p	0.5 - 4 mm
Cutting conditions	slightly interrupted
Feed f	0.1 - 0.4 mm/rev.

Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 120412
Number of changes/inserts	8
Type of product	Indexable insert for turning