

Garant**DNMG 150604, Grade: HB7140-1**

Order data

Order number	250658 HB7140-1
GTIN	4045197820440
Item class	21G

Description

DNMG 150604 HB7140-1 Grade: HB7140-1
Chip breaker: VS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 70 - 260 m/min

Technical description

Grade	HB7140-1
Cutting conditions	slightly interrupted
Cutting speed v_c main application	70 - 260 m/min
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.4 mm
Cutting depth a_p	0.3 - 2 mm
Main application	M

Chip breaker	VS
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DNMG 150604
Number of changes/inserts	4
Type of product	Indexable insert for turning