

Kroepelin
Längenmesstechnik

External quick caliper with dial gauge, Measuring range: 0-20 mm



Order data

Order number	438550 0-20
GTIN	2050001036759
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Protection class **IP65**.

Application:

For quick measuring of external grooves, wall thicknesses, plates, pipe wall thicknesses, foils etc.

Norm: Manufacturer's standard

Calibration: C7

IP Index of Protection: IP 65

Scale divisions: 0.01 mm

Error limit: 0.03 mm

Carbide spherical point \varnothing : 1.5 mm

maximum contact point length L (measurement depth): 80 mm

Dial indicator \varnothing : 60 mm

Technical description

Measuring range	0 - 20 mm
maximum contact point length L (measurement depth)	80 mm
Scale divisions	0.01 mm
Carbide spherical point \varnothing	1.5 mm
Dial indicator \varnothing	60 mm

IP Index of Protection	IP 65
Error limit	0.03 mm
Norm	Manufacturer's standard
Measurement technology	analogue
Calibration	C7
Type of product	External quick calipers

Services

Calibration External / internal quick caliper	013850
Labelling laser-etched Type	018940
DAkkS calibration External / internal quick caliper	011320