


**Kroeplin**  
Längenmesstechnik

## External quick caliper with dial gauge, Measuring range: 0-50 mm



### Order data

Order number	438550 0-50
GTIN	2050001036766
Item class	46Q

### Description

#### Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Protection class **IP65**.

#### Application:

For quick measuring of external grooves, wall thicknesses, plates, pipe wall thicknesses, foils etc.

Norm: Manufacturer's standard

Calibration: C7

IP Index of Protection: IP 65

Scale divisions: 0.05 mm

Error limit: 0.05 mm

Carbide spherical point  $\varnothing$ : 3 mm

maximum contact point length L (measurement depth): 167 mm

Dial indicator  $\varnothing$ : 60 mm

### Technical description

Dial indicator $\varnothing$	60 mm
maximum contact point length L (measurement depth)	167 mm
Scale divisions	0.05 mm
Measuring range	0 - 50 mm

Carbide spherical point Ø	3 mm
IP Index of Protection	IP 65
Error limit	0.05 mm
Norm	Manufacturer's standard
Measurement technology	analogue
Calibration	C7
Type of product	External quick calipers

### Services

Calibration External / internal quick caliper	013850
Labelling laser-etched Type	018940
DAkkS calibration External / internal quick caliper	011320