

Kroepelin
Längenmesstechnik

Internal quick caliper, Measuring range: 30-50mm



Order data

Order number	438950 30-50
GTIN	2050001036872
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

maximum groove depth	7 mm
Carbide spherical point Ø	1 mm
minimum groove width	1.5 mm
maximum contact point length L (measurement depth)	80 mm
Measuring range	30 - 50 mm
Scale divisions	0.01 mm
Error limit	0.03 mm
Dial indicator Ø	65 mm
Calibration	C7
IP Index of Protection	IP 65

Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Internal quick caliper

Services

DAkkS calibrationExternal / internal quick caliper Type S	023460 S
CalibrationExternal / internal quick caliper Type S	023450 S