


Garant
SNMG 120412, Grade: HB7120-1


Order data

| | |
|--------------|-----------------|
| Order number | 251326 HB7120-1 |
| GTIN | 4045197819987 |
| Item class | 21G |

Technical description

| | |
|--------------------------------------|--------------------|
| Cutting conditions | continuous |
| Chip breaker | VG |
| Corner radius | 1.2 mm |
| Grade | HB7120-1 |
| Feed f | 0.25 - 0.8 mm/rev. |
| Cutting depth a_p | 1.5 - 9 mm |
| Cutting speed v_c main application | 70 - 240 m/min |
| Main application | M |
| Finishing/roughing assignment | Roughing |
| Tool material | Carbide |
| ISO code indexable insert | SNMG 120412 |

| | |
|---------------------------|------------------------------|
| Number of changes/inserts | 8 |
| Type of product | Indexable insert for turning |