

Kroepelin
Längenmesstechnik

Internal quick caliper with long contact points, Measuring range: 15-65mm



Order data

Order number	438953 15-65
GTIN	2050001743138
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

minimum groove width	2.5 mm
Measuring range	15 - 65 mm
Scale divisions	0.05 mm
maximum contact point length L (measurement depth)	188 mm
maximum groove depth	4.5 mm
Carbide spherical point \varnothing	1.5 mm
Error limit	0.05 mm
Dial indicator \varnothing	66 mm
Calibration	C7
IP Index of Protection	IP 65
Standard	Manufacturer's standard

Measurement technology	analogue
Type of product	Internal quick caliper

Services

DAkkS calibrationExternal / internal quick caliper Type S	023460 S
CalibrationExternal / internal quick caliper Type S	023450 S